## FRONT-ROLLER PLUS



## Front pannier (pair) with roll closure and QL2.1 system



Handle for mounting and releasing the QL2 system

Additional closure with buckle and D-ring (when the bag is carried with the shoulder strap)

Buckles for closing the rolling closure at the

Highly reflective 3M Scotchlite reflector

top or for attaching the shoulder strap

Shoulder strap with padding for comfortable carrying or for fixing to the hook













Release handle for mounting and releasing the QL2.1 system

Automatically locking QL2.1 hooks with 16 mm diameter

Exchangeable hook inserts in sizes 8, 10 and 12 mm

Slidable and rotatable hook (15° steps) with anti-scratch function  $\,$ 

Hook rail made of two-component synthetic with anti-scratch function

- Edge protector with slots for mounting the ORTLIEB carrying system

Height cm/in.	Width cm/in.	Depth cm/in.	Vol. I/cu.in.	Weight g/oz.
30/11,8	25/9,8	14/5,5	25/1526 (pair)	1440/50,8 (pair)

- · Classical pannier (pair) with roll closure
- · Abrasion restistant Cordura fabric
- · QL2.1 system for racks up to 16 mm
- · 20 mm hook available as separate accessory (e.g. for e-bikes)
- · Including reduction pieces for tube diameters 8, 10 and 12 mm; with anti-scratch function reducing abrasions on rack
- ·Top QL hooks and lower sliding hook adjustable without requiring any tools
- · Lower hook rail made of two-component "hard-soft" synthetic reduces abrasions on carrier
- · Can be used individually or as a pair for rear or front rack (low-rider)
- · Can be combined with the ORTLIEB Rack-Pack
- · Including integrated inner pocket
- · Simultaneous use of ORTLIEB Travel-Biker or Trunk-Bag possible
- · Highly reflective 3M Scotchlite reflectors
- · Comfortable to carry (shoulder strap included)
- · Ideal for the use on children's/youth bicycles
- · Can be easily cleaned inside
- $\cdot \text{ Optional accessories: ORTLIEB carrying system, outer pocket/s size S, mesh pocket, bottle cage, QL 2.1 hook 20 \ mm}$

Panniers come as a pair with 2 shoulder straps and reduction inserts for 8, 10 and 12 mm (two pairs per size)

Note: In order to meet standard IP64 (6=dustproof, 4=protected against splash water coming from all directions) the closure must be rolled 3-4 times.

